

TECHSPEC® 30mm Dia. x 50mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#47-713-INK** 3-5 DAYS

[Other Coating Options](#)

− 1 +

A\$233.60

ADD TO CART

Qty 1-5
A\$233.60
Qty 6+
A\$186.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Effective Focal Length EFL (mm):
50.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 42.57
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 29.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 13.20 ±0.20
Center Thickness CT 1 (mm) : 11.00 ±0.10
Center Thickness CT 2 (mm) : 2.20 ±0.10
Radius R₁ (mm) : 34.81
Radius R₂ (mm) : -22.12
Radius R₃ (mm) : -203.48
Edge Thickness ET (mm) : 9.25
Substrate : ☐ N-BAF10 / N-SF10
Surface Quality : 40-20
f/# : 1.67
Numerical Aperture NA : 0.30
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015 : Compliant
Reach 209 : Compliant
Certificate of Conformance : View