

TECHSPEC[®] 30mm, Metric Z-Stage



TECHSPEC[®] Vertical Translation Stages



[+1](#)

Stock **#66-496** 1 In Stock

-

1

+

A\$1,032^{.00}

ADD TO CART

Volume Pricing	
Qty 1-2	A\$1,032.00 each
Qty 3+	A\$900.48 each
Need More?	Request Quote

Product Downloads

General

Type:

Metric

Physical & Mechanical Properties

Type of Movement:

Linear (Z)

Guide System:

Crossed Roller Bearing	
30 x 30	Stage Size (mm):
	Travel (mm):
5	
M6 x 1	Center Hole:
	Construction:
Aluminium Stage	
0.5	Leadscrew Pitch (mm):
	Load Capacity (kg):
1.5	
1.18 x 1.18	Stage Size (inches):
	Straight Line Accuracy (µm):
3	

Hardware & Interface Connectivity

Type of Drive:	
Lead Screw	

Threading & Mounting

Mounting Threads:	
(1) M6 x 1, (8) M2 x 0.4	

Regulatory Compliance

RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
REACH 241:	
Compliant	

Product Details

[Bottom adapter plates](#), sold separately, are required to mount 30mm and 40mm stages to standard breadboards.

- Mechanically Compatible with our [TECHSPEC® Stages](#)
- Fine Micrometer Movement
- Locking Screw on Stages

Our newly developed precision TECHSPEC® Vertical Translations Stages (Z-axis stages) feature a unique and advanced crossed roller bearing guide system that provides high accuracy, rigidity and load capacity. Each stage is designed to integrate with our line of [TECHSPEC® stages](#) in order to provide flexibility in allowing the user to create a number of multi-axis configurations. These stages have a locking screw and fine micrometer movement. TECHSPEC® Vertical Translations Stages are constructed of aluminum and have a linear (Z) movement. The stages are available in both English and Metric versions and are offered in four sizes.

Technical Information

