

32.5mm Dia. x 23.5mm FL, Aspheric Condenser Lens



Stock #19-519

3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$75.20

ADD TO CART

Qty 1-10
A\$75.20
Qty 11+
A\$67.20
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
32.50 +0.0/-0.2

Effective Focal Length EFL (mm):
23.50

Numerical Aperture NA:
0.69

Back Focal Length BFL (mm):

Substrate: □
H-K51

Focal Length Tolerance (%):
±5

Coating:
Uncoated

Centering (arcmin):
≤30

Surface Quality:
80-50 (typical)

Clear Aperture CA (mm):
29.25

Edge Thickness ET (mm):
1.85

Center Thickness CT (mm):
13.50 ±0.30

f##:
0.72

Bevel:
Protective bevel as needed

Diameter of Asphere (mm):
32.5

Radius R₂ (mm):
165

Shape of Back Surface:
Convex

Type:
Condenser Lens

Wavelength Range (nm):
350 - 2000

Conjugate Distance:
Infinite

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)