

[See all 8 Products in Family](#)

## 34mm<sup>2</sup> Suppressed NIR DUV Photodiode w/Metal Housing



DUVPhotodiodes

Stock #84-599 **5 In Stock**

⊖ 1 ⊕ A\$206<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	A\$206.40 each
Qty 5-9	A\$182.40 each
Qty 10-24	A\$162.40 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

2 @ 0 V, 1 kΩ **Rise Time (μs):**

### Physical & Mechanical Properties

5.8x5.8 **Size of Active Area (mm):**

34.0 **Active Area (mm<sup>2</sup>):**

## Optical Properties

720.00 **Peak Response Wavelength (nm):**

## Electrical

0.36 **Responsivity @ 980nm (AW):**

**Shunt Resistance @ V=-10mV (GΩ):**  
Minimum: 0.5  
Typical: 5

0.34 **Responsivity @ 633nm (AW):**

0.12 **Responsivity @ 200nm (AW):**

800.00 **Capacitance @ V<sub>R</sub>=0V (pF):**

**Noise Equivalent Power NEP (W/ Hz<sup>1/2</sup>):**  
1.6 x 10<sup>-14</sup> @ 0 V, 200nm

5.00 **Maximum Reverse Voltage (V):**

## Hardware & Interface Connectivity

TO-8 **Connector:**

## Environmental & Durability Factors

-20 to +60 **Operating Temperature (°C):**

-55 to +80 **Storage Temperature (°C):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Excellent UV Sensitivity
- High Shunt Resistance
- Low Capacitance

DUV Photodiodes are ideal for a wide variety of applications, including UV spectrophotometry and analytical and medical instrumentation. DUV Photodiodes are designed for enhanced responsivity from 200 – 400nm, and with sensitivity extending down to 190nm. DUV Photodiodes feature quartz windows and either metal or ceramic housing. Models with suppressed NIR performance are also available.