

TECHSPEC<sup>®</sup> 30mm ID Fixed Angle Mounting Plate



30mm ID Fixed Angle Mounting Plate, #85-622

Stock **#85-622** 2 In Stock

-

1

+

A\$91<sup>20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | A\$91.20 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Angle Adjustment

Function:

Physical & Mechanical Properties

30.0

Plate Inner Diameter (mm):

38.0

Bolt Circle Diameter for M3 C**h**ore (mm):

Black Anodized Aluminum

Construction:

|                       |                             |
|-----------------------|-----------------------------|
| 50 Dia.               | Dimensions (mm):            |
| 10.00                 | Thickness (mm):             |
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Compliant             | REACH 241:                  |

## Product Details

- Multiple Angular Positioning Options
- Fixed and Continuous Adjustment Plates Available
- Anodized Aluminum Construction

TECHSPEC® Cage System Angle Adjustment Plates attach to [standard mounting plates](#) via angle brackets, and offer a range of angular positioning options. The fixed angle mounting plates feature M3 C-Bore holes positioned at 30° increments to introduce 30°, 60°, or 90° bends in the optical path. Swivel adapter plates are designed to be used in pairs, and enable continuous angle adjustment. [#85-692](#) or [#85-701](#) post adapter for 25mm plates serves as a joint between two swivel adapter plates. Suspending a tilt plate between two standard cage system plates allows an optic or mount to be tilted with respect to the optical axis.

### Quick Video Demonstration

Maximize your application performance with the right products. View a quick video demonstration of TECHSPEC Cage System components: [How to Build a Swivel Joint Assembly](#).