

TECHSPEC[®] 30R/70T NIR, C-Mounted Plate Beamsplitter



Stock **#49-687** [CONTACT US](#)

-

1

+

A\$534^{.40}

ADD TO CART

Volume Pricing	
Qty 1-4	A\$534.40 each
Qty 5-9	A\$467.20 each
Qty 10+	A\$438.40 each
Need More?	Request Quote

Product Downloads

General

Type:

Standard Beamsplitter

Beamsplitter Included:

Standard 30R/70T NIR Plate Beamsplitter, 1 λ

Physical & Mechanical Properties

Construction:

Plate

+0.0/-0.25	Dimensional Tolerance (mm):
38.0	Extension Length (mm):
Black Anodized Aluminum	Housing:

38 x 38 x 50	Housing Dimension:
--------------	--------------------

Optical Properties

Surface 2: Multi-Layer Anti-Reflection for Near-Infrared Region	Coating Specification:
30/70	Reflection/Transmission Ratio (R/T):

±5	Reflection/Transmission Tolerance (%):
N-BK7	Substrate: ☐

1λ	Surface Flatness (P-V):
60-40	Surface Quality:

700 - 1100	Wavelength Range (nm):
------------	------------------------

Threading & Mounting

C-Mount Enclosure	Mount:
C-Mount (1" x 32 TPI)	Thread Type:

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Pre-Mounted 90 Degree Interface
 - Four C-Threaded Mounting Holes
 - Several Beamsplitting Options Available
 - Additional C-Mounted [Beamsplitters](#), [Filters](#), and [Mirrors](#) Available
- TECHSPEC® C-Mounted Plate Beamsplitters are designed to simplify system integration. These mounted beamsplitters include a TECHSPEC® Plate Beamsplitter pre-mounted in an Aluminum cube designed to interface with C-Mount (1" x 32 TPI) systems. Each cube is configured with four C-threaded holes, one on each face, and a ¼-20 tapped hole on the base for post mounting. TECHSPEC® C-Mounted Plate Beamsplitters are available in 30R/70T, 50R/50T, and 70R/30R options for either the visible or near infrared spectrum.

The C-Mounted Visible Plate Beamsplitters are designed for the 400 - 700nm wavelength range and the C-Mounted NIR Plate Beamsplitters are designed for the 700 - 1100nm wavelength range.

Note: These products cannot be disassembled. For mounting an alternative beamsplitter in a C-Mount Cube, use either [#56-264](#) or [#56-265](#).

Technical Information



