

[See all 1 Products in Family](#)

## 32mm Dia. x -200mm FL, Grade 2, Double-Concave Lens



Stock #53-113 CLEARANCE **20+ In Stock**

1  **A\$18<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1+	<b>A\$18.00</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Double-Concave Lens **Type:**

#### Physical & Mechanical Properties

32.00 **Diameter (mm):**

#### Optical Properties

-200.00 **Effective Focal Length EFL (mm):**

**f#:**

6.25

Numerical Aperture NA:

0.08

## Material Properties

Grade 2

Grade:

## Regulatory Compliance

[View](#)

Certificate of Conformance:

## Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Double-concave (DCV) lenses have two inward curved surfaces and a negative focal length. They are used for image reduction and to spread light.

Experimental Quality Double-Concave (DCV) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

**Note:** Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

## Technical Information

