

355nm High Performance Laser Line Filter 12.5mm Dia.



High Performance Laser Line Bandpass Filters

Stock **#64-240** **1 In Stock**

☐ [Additional Bandwidths](#)

-

1

+

A\$638⁴⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$638.40 each
Need More?	Request Quote

Product Downloads

General	
Bandpass Filter	Type:
Physical & Mechanical Properties	
12.50 +0.0/-0.1	Diameter (mm):
≥10	Clear Aperture CA (mm):
±0.10	Thickness Tolerance (mm):

Mounted in Black Anodized Ring	Construction:
Physical Durability: ML-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3	
Substrate Thickness (mm):	
2.0 ±0.1	

Optical Properties

0 ±2	Angle of Incidence (°):
1.3	Bandwidth (nm):
Beam Deviation (arcsec):	
<11	
OD 5 Blocking Wavelength Range (nm) : 315 - 352 & 359 - 423	
OD 6 Blocking Wavelength Range (nm): 327 - 350 & 360 - 390	
Optical Density OD (Average):	
≥6.0	
Center Wavelength CWL (nm):	
355.00	
Design Wavelength DWL (nm):	
355	
Full Width-Half Max FWHM (nm):	
1.35 - 2.49	
Substrate:	
Fused Silica	
Minimum Transmission (%):	
>90	
Coating:	
Hard Coated	
Surface Quality:	
60-40	
Transmission (%):	
>90	
Blocking Wavelength Range (nm): 315 - 352 & 359 - 423	
Transmitted Wavefront, P-V: ¼ @ 633nm	

Threading & Mounting

Mount Thickness (mm):	
3.5 ±0.1	

Environmental & Durability Factors

Temperature Dependence (ppm/°C):	
<5	
Environmental Durability: ML-STD-810F Paragraphs 501.4, 502.4, and 507.4	

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 209:
Certificate of Conformance:	
View	

Product Details

- Over 90% Transmission at Specified Laser Lines
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, High Performance Laser-Line Bandpass Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. These laser line filters are available at popular diode and Nd:YAG laser lines, including 532nm, 785nm, and 1064nm. High Performance Laser-Line Bandpass Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, High Performance Laser-Line Bandpass Filters are excellent complements to TECHSPEC® Notch Filters and [Laser Line Longpass Filters](#).

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). Atypical LIDT for these filters is 0.1 J/cm² @ 532nm, 10ns.

Technical Information



Compatible Mounts