

355nm, 25.4mm Dia., 1x6 Spot Array, Diffractive Beamsplitter



HOLO/OR Diffractive Beamsplitters

Stock #14-690 3-5 DAYS

⊖ 1 ⊕

A\$2,856.00

ADD TO CART

Qty 1+
A\$2,856.00

Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
22.9

Coating:
Laser V-Coat (355nm)

Design Wavelength DWL (nm):
355

Diameter (mm):
25.40 +0.05/-0.15

Substrate:
[Fused Silica](#) (Corning 7980)

Thickness (mm): 3.00 ±0.1
Input Beam Mode: SMor MM
Minimum Beam Diameter (mm): 0.48
Overall Efficiency (%): 82
Full Angle (°) : 1.27
Output Number of Spots: 6
Separation Angle (°): 0.25
Uniformity (%): <5
Zero Order, Relative to the Incident Beam (%): <1.5
Damage Threshold, Reference: ☐ See Link for More Details

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant