

TECHSPEC® 355nm CWL, 25mm Dia, 1.3nm Bandwidth, OD 6 Laser Line Bandpass Filter



Stock **#68-958**

CONTACT US

[Additional Bandwidths](#)

-

1

+

A\$1,176^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	A\$1,176.00 each
Qty 6-25	A\$940.80 each
Need More?	Request Quote

Product Downloads

General

Type:

Bandpass Filter

Physical & Mechanical Properties

Diameter (mm):

25.00

Clear Aperture CA (mm):

21.00

Thickness Tolerance (mm):

+0.0/-0.1	
Optical Properties	
0 ±2	Angle of Incidence (°):
1.3	Bandwidth (nm):
OD 5 Blocking Wavelength Range (nm) : 314.8 - 351.8 & 358.6 - 422.5	
OD 6 Blocking Wavelength Range (nm): 326.6 - 349.7 & 360.3 - 390.5	
≥6.0	Optical Density OD (Average):
355.00	Center Wavelength CWL (nm):
355	Design Wavelength DWL (nm):
2.50	Full Width-Half Max FWHM (nm):
Fused Silica (Corning 7980)	Substrate: ☐
Hard Coated	Coating:
60-40	Surface Quality:
≥80	Transmission (%):
λ/4 @ 633nm	Transmitted Wavefront, RMS:

Threading & Mounting

3.5	Mount Thickness (mm):
-----	-----------------------

Environmental & Durability Factors

Durability:	
Environmental: ML-STD-810F, sect. 507.4	
Durability: MIL-C-48497A, sect. 3.4.1	

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Over 90% Transmission at Design Wavelength
 - Hard Coated Design
 - Designed for Laser Applications
- Available for use with common gas and solid state lasers, TECHSPEC OD 6 Laser Line Clean-Up Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisyspontaneous emission. TECHSPEC OD 6 Laser Line Clean-Up Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, TECHSPEC Laser Line Clean-Up Filters are excellent complements to [TECHSPEC Notch Filters](#) or [TECHSPEC Raman Longpass Edge Filters](#).

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

Technical Information





Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts

