

TECHSPEC® 35mm 632.8nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock #47-568 **9 In Stock**

⊖ 1 ⊕ A\$780⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$780.80 each
Qty 6-25	A\$632.00 each
Qty 26-99	A\$574.40 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

Protective as needed **Bevel:**

90.00 **Clear Aperture (%):**

Cube **Construction:**

35.0 x 35.0 x 35.0 ±0.1 **Dimensions (mm):**

Optical Properties

±3 **Beam Deviation (arcmin):**

$R_{\text{abs}} < 0.25\%$ @ 632.8nm **Coating Specification:**

632.8 **Design Wavelength DWL (nm):**

1000:1 **Extinction Ratio:**

>95 **P-Polarization Transmission (%):**

>99.5 **S-Polarization Reflection (%):**

[N-BK7](#) **Substrate:**

40-20 **Surface Quality:**

1.25 **Power (fringes) @ 632.8nm:**

0.25 **Irregularity (fringes) @ 632.8nm:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**


[Compliant](#) **Reach 219:**

[View](#) **Certificate of Conformance:**

Product Details

- Designed for Common Diode, Gas, and Solid State Lasers
- Reflects S-Polarized Light, Transmits P-Polarized Light
- High Extinction Ratio

TECHSPEC® Laser Line Polarizing Cube Beamsplitters split randomly polarized beams into two orthogonal, linearly polarized components. S-polarized light is reflected at a 90° angle, while P-polarized light is transmitted. The beamsplitters consist of a pair of precision [right angle prisms](#) cemented together to minimize transmitted wavefront distortion, and to provide excellent parallelism between incoming and transmitted beams. TECHSPEC® Laser Line Polarizing Cube Beamsplitters are designed for many common laser wavelengths and have a high extinction ratio. These beamsplitters are designed for common diode, gas, and solid-state laser applications.



LASER OPTICS MADE BY EDMUND OPTICS® [LEARN MORE](#)

Technical Information

