

[See all 49 Products in Family](#)

**TECHSPEC® 35mm f/5.6, UCi Series Fixed Focal Length Lens**



35mm UCi Series Fixed Focal Length Lens



Stock **#33-900** **2 In Stock**

⊖ 1 ⊕ **A\$363<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$363.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

UCi Series	<b>Product Family:</b>
Fixed Focal Length Lens	<b>Type:</b>
No	<b>IR Cut Filter:</b>

**Physical & Mechanical Properties**

Fixed Iris Option:

52.19 Length (mm):

26.5 Maximum Diameter (mm):

26.5 Outer Diameter (mm):

2.21 Maximum Rear Protrusion (mm):

52.19 Maximum Length (mm):

## Optical Properties

Horizontal Field of View @ Max Sensor Format:  
45.6mm - 11.9°

Field of View at Max Sensor Format:  
Horizontal: 45.6mm - 11.9°  
Vertical: 34.1mm - 8.9°  
Diagonal: 57.2mm - 14.8°

Horizontal Field of View, 1/1.8" Sensor:  
45.6mm - 11.9°

Horizontal Field of View, 1/2" Sensor:  
40.5mm - 10.6°

Horizontal Field of View, 1/2.5" Sensor:  
36.7mm - 9.6°

Horizontal Field of View, 1/3" Sensor:  
30.3mm - 7.9°

Horizontal Field of View, 1/4" Sensor:  
22.7mm - 6.0°

9.00 Maximum Image Circle (mm):

0.013 Numerical Aperture NA, Object Side:

7 (5) Number of Elements (Groups):

35.00 Focal Length FL (mm):

200 - ∞ Working Distance (mm):

f/5.6 Aperture (f/#):

M4 MgF<sub>2</sub> Coating:

M4 MgF<sub>2</sub> Coating Specification:

34.01 Entrance Pupil Position (mm):

49.25 Object Space Principal Plane (mm):

-19.45 Image Space Principal Plane (mm):

-0.22 Maximum Distortion (%):

-46.71 Exit Pupil Position (mm):

VIS Lens Wavelength Range:

## Sensor

1/2.5" Optimized Sensor Format:

1/1.8" Maximum Sensor Format:

1.85 Pixel Size (µm):

## Threading & Mounting

N/A Filter Thread:

C-Mount Mount:

## Environmental & Durability Factors

Storage Temperature (°C):

Type of Ruggedization:  
Industrial (Fixed Aperture with Simplified Mechanics)

## Regulatory Compliance

Certificate of Conformance:  
[View](#)

## Product Details

- Up to 1/1.8", C-Mount, S-Mount Lens
- Up to 12 MegaPixels, 1.85µm Pixel Size Sensors
- Instrumentation (UCi) versions of our UC Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 4mm to 35mm Focal Length

TECHSPEC® UCi Series Fixed Focal Length Lenses utilize the same optics as the TECHSPEC UC Series Lenses and feature 4K resolution. These lenses are designed for small pixels  $\leq 2.2\mu\text{m}$  and offer a wide range of fixed apertures for a variety of applications. While optimized for 1/2.5" sensors, many focal length options can be used on sensors up to 1/1.8". TECHSPEC® UCi Series Fixed Focal Length Lenses are ideal for OEM applications that require small, robust, and lightweight imaging solutions.

**Note:** For adjustable aperture options, see our [TECHSPEC® UC Series Fixed Focal Length Lenses](#).

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:


**UC Series:** Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

**UCi Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.


**UCr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

**UCw Series:** Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.


## Technical Information




#33-900, 35mm f/5.6, UCi Series Fixed Focal Length Lens, Distortion Plot



#33-900, 35mm f/5.6, UCi Series Fixed Focal Length Lens, Relative Illumination Plot




#33-900, 35mm f/5.6, UCi Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#33-900, 35mm f/5.6, UCI Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 400mm Working Distance, f5.6



#33-900, 35mm f/5.6, UCI Series Fixed Focal Length Lens, Depth of Field Plot, 400mm Working Distance, f5.6



#33-900, 35mm f/5.6, UCI Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 750mm Working Distance, f5.6



#33-900, 35mm f/5.6, UCI Series Fixed Focal Length Lens, Depth of Field Plot, 750mm Working Distance, f5.6

## Compatible Cameras