

[See all 13 Products in Family](#)

## 365nm, Ethernet High Intensity Coaxial Spot Light (Recertified 05-P)

See More by [Advanced Illumination](#)



Advanced Illumination Ethernet Controlled High Intensity LED Spot Lights

Stock **#21-356-RCD-05P** RECERTIFIED **1 In Stock**

⊖ 1 ⊕ **A\$848<sup>.00</sup>**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | A\$848.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

|                 |                              |
|-----------------|------------------------------|
| SL162-365C1     | <b>Model Number:</b>         |
| 50,000          | <b>LED Lifetime (hours):</b> |
| 1               | <b>Number of LEDs:</b>       |
| LED Illuminator | <b>Type of Illumination:</b> |

**Note:**  
Required Controller [#18-645](#); Required Power Supply [#66-855](#)

**Manufacturer:**  
Advanced Illumination

**Geometry:**  
Spot Light

**Illumination Mode:**  
Constant, Pulsed, Gated

## Physical & Mechanical Properties

**Weight (g):**  
85.1

## Optical Properties

**Color:**  
UV

**Wavelength (nm):**  
365

## Hardware & Interface Connectivity

**Connector:**  
C1

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#66-855](#)  
Europe: [#66-855](#)  
Japan: [#89-513](#)  
Korea: [#33-773](#)  
China: [#66-855](#)

**Length of Cable (m):**  
2

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +60

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details

- Controllable via Ethernet GUI or Web Browser
- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Ports
- Efficient Thermal Management for Long LED Life
- Compatible with [TECHSPEC® Telecentric Backlight Illuminators](#) and [Lenses](#)

Advanced Illumination Ethernet Controlled High Intensity In-Line Lights utilize a C1 connector to connect to the DCS-100E Single Output Controller (#18-645). The DCS-100E Single Output Controller allows these high intensity in-line lights to be ethernet controlled through a downloadable software package or through a Web Based Graphical User Interface (GUI). With efficient thermal management, these in-line lights are able to provide 33,000 Lux at a working distance of 100mm with a spot size of 61mm in either a continuous, pulsed, or gated operating mode. Advanced Illumination Ethernet Controlled High Intensity In-Line Lights can be overdriven in short pulses without damaging the LED through Advanced Illumination's SignaTech™ Control System which is available with the DCS-100E Controller. These lights are available in UV, Blue, Green, Red Orange, IR, or White and are compatible with the 8mm port found on many in-line illumination imaging lenses, making them an excellent choice for use with TECHSPEC® Telecentric Backlight Illuminators and telecentric lenses with an [inline illumination port](#). For applications that do not require ethernet controlled functionality, [Advanced Illumination High Intensity In-Line Lights](#) are also available.

**Note:** 24V power supply ([#66-855](#)) and DCS-100E Single Output Controller ([#18-645](#)) are required for use.