

TECHSPEC® 36mm EFL MgF₂ Coated, UV-to-NIR Corrected Triplet



Stock #65-033

3-5 DAYS

-

1

+

A\$4,120.00

ADD TO CART

Qty 1-5
A\$4,120.00
Qty 6+
A\$3,502.40
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
36.00

Focal Length Tolerance (%):
±0.5 @ 248nm

Back Focal Length BFL (mm):
24.98

Back Focal Length BFL from Housing (mm):
24.50

Clear Aperture CA (mm): 22.50
Substrate: CaF₂ / Fused Silica / CaF₂
Surface Quality: 60-40
f#: 1.6
Numerical Aperture NA: 0.31
Coating: MgF₂ (193-1000nm)
Coating Specification: MgF₂ @ 600nm
Effective Focal Length EFL @ 248nm (mm): 36.00
Housing Diameter (mm): 30.00 ±0.05
Housing Length (mm): 27.00 ±0.05
Type: Achromatic Triplet Lens
Wavelength Range (nm): 193 - 1000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View