

[See all 10 Products in Family](#)

TECHSPEC®

3.6mm FL, Red Series M12 Lens



3.6mm Focal Length, #57-907

Stock **#57-907** 20+ In Stock

-

1

+

A\$144⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-49	A\$144.00 each
Qty 50+	A\$114.00 each
Need More?	Request Quote

Product Downloads

General	
Red Series	Series:
M12 Imaging Lens	Type:
No	IR Cut Filter:
Standard Lens	Imaging Lens Type:

Physical & Mechanical Properties	
Fixed	Iris Option:
14.60	Length (mm):
14	Maximum Diameter (mm):
14	Outer Diameter (mm):
4	Weight (g):
Optical Properties	
Horizontal Field of View @ Max Sensor Format: 791.6mm - 89.1°	
Field of View at Max Sensor Format: Horizontal: 790.8mm - 89° Vertical: 435.1mm - 56.7° Diagonal: 1037mm - 104.6°	
Horizontal Field of View, 1/3" Sensor: 791.6mm - 89.1°	
Horizontal Field of View, 1/4" Sensor: 499.4mm - 63.6°	
5.60	Maximum Image Circle (mm):
0.0017	Numerical Aperture NA, Object Side:
100 lp/mm @ 20% Contrast	Resolution, On-Axis:
100 lp/mm @ 20% Contrast	Resolution, Full Field:
4 (3)	Number of Elements (Groups):
400 - 700	Wavelength Range (nm):
3.60	Focal Length FL (mm):
400 - ∞	Working Distance (mm):
f/2.5	Aperture (f/#):
-38.51 @ Full Field	Distortion (%):
4.32 - 4.30	Back Focal Length BFL (mm):
λ/4 MgF ₂	Coating:
λ/4 MgF ₂ @ 550nm	Coating Specification:
2.68	Entrance Pupil Position (mm):
5.03	Object Space Principal Plane (mm):
1.69	Image Space Principal Plane (mm):
-38.51	Maximum Distortion (%):
-5.83	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:
Sensor	
1/3.2"	Maximum Sensor Format:
5.00	Pixel Size (μm):
Threading & Mounting	
N/A	Filter Thread:
S-Mount (M12 x0.5)	Mount:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Up to 1/2", S-Mount Lens
- Up to 1.3 MegaPixels, 5µm Pixel Size Sensors
- Board Camera Lens Optimized Long WD and Infinite Conjugate
- 3.6mm to 8mm Focal Lengths


TECHSPEC® Red Series M12 Lenses feature a high resolution, all glass element design. The slight negative (barrel) distortion can be easily factored out since the Angular Field of View is increased, thereby offering more workable field of view (FOV) in the object domain. Threaded for M12 x0.5, these lenses are optimized for 1/3" and 1/2" sensor formats. TECHSPEC® Red Series M12 Lenses are ideal for demanding imaging applications. Prescription data is available by submitting a [Request for Prescription Form](#).

Note: Compatible [TECHSPEC® M12 Imaging Lens Accessories](#) available.


Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- **Blue Series M12 Lenses:** High resolution finite conjugate designs optimized for machine vision working distances.
- **Rugged Blue Series M12 Lenses:** [Stabilized ruggedization](#) versions of our Blue Series M12 Lenses, utilizing the same optics.
- **Green Series M12 Lenses:** Finite conjugate designs optimized for machine vision working distances.
- Red Series M12 Lenses: Infinite conjugate designs optimized for high resolution performance out to infinity.
- **HEO Series M12 Lenses:** Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- **Liquid Lens M12 Lenses:** Integrated liquid lens for fast electronic focus.


Technical Information




#57-907, 3.6mm FL, Red Series M12 Lens, Distortion Plot



#57-907, 3.6mm FL, Red Series M12 Lens, Relative Illumination Plot



#57-907, 3.6mm FL, Red Series M12 Lens, Modulated Transfer Function (MTF) Plot, 3000mm Working Distance, f2.5



#57-907, 3.6mm FL, Red Series M12 Lens, Depth of Field Plot, 3000mm Working Distance, f2.5

Focal Length	A	B	C	D
3.6	14	14.6	4.5	4.2
4.4	14	24	6.4	3.8
6.4	14	30	10.2	3.8
7.2	14	22.1	8.3	4.0
8.0	14	15	8.7	4.0

Units: mm