


TECHSPEC® 35mm Protected Silver Coated, N-BK7 Right Angle Mirror



Stock **#89-632** 3-5 DAYS

- 1 + **A\$292.00**

ADD TO CART

Qty 1-5
A\$292.00
Qty 6+
A\$233.60
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: □
[N-BK7](#)

Surface Quality:
40-20

Length of Legs (mm):

35.00
Dimensional Tolerance (mm): ±0.1
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 44.55 x 31.50
Length of Hypotenuse (mm): 49.50
Type: Right Angle Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant