

38.1mm Dia., 3mm Thick, 7 - 14μm, ISP Optics Zinc Selenide IR Beamsplitter

See More by [ISP Optics](#)



Stock #25-030 3-5 DAYS

-

1

+

A\$760.00

ADD TO CART

Qty 1+

A\$760.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
45

Clear Aperture (%):
85

Construction:
Plate

Diameter (mm):
38.10 +0.00/-0.13

Parallelism (arcmin): <3
Reflection/Transmission Ratio (R/T): 50/50 ±10% @ 7 - 14µm
Substrate: Zinc Selenide (ZnSe), CVD Grade
Surface Flatness (P-V): 2λ @ 633nm
Surface Quality: 60-40
Thickness (mm): 3.00 ±0.13
Type: Standard Beamsplitter
Wavelength Range (µm): 7 - 14
Wavelength Range (nm): 7000 - 14000
Model Number: BSP50-ZC-38-3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View