


[See all 10 Products in Family](#)

38.1mm Dia., Aluminum Coated, Aluminum Substrate Mirror



Metal Substrate Mirrors

Stock #47-115 **17 In Stock**

- 1 + A\$380⁰⁰

ADD TO CART

Volume Pricing

Qty 1-5	A\$380.80 each
Qty 6-25	A\$344.00 each
Qty 26-49	A\$324.80 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror **Type:**

Physical & Mechanical Properties

38.10 +0.00/-0.38 **Diameter (mm):**

9.50 **Thickness (mm):**

90 Clear Aperture (%):

<175 Surface Roughness (Å):

Optical Properties

0.4 - 12 Wavelength Range (µm):

Metal Coating Type:

Protected Aluminum (400-12000nm) Coating:

400 - 12000 Wavelength Range (nm):

Aluminum 6061-T6 Substrate: □

Coating Specification:
R_{avg} >85% @ 400 - 700nm
R_{avg} >70% @ 700 - 2000nm
R_{avg} >97% @ 2 - 12µm

80-50 Surface Quality:

λ/4 Surface Flatness (RMS):

Threading & Mounting

6-32 TPI Tapped Holes Mounting Threads:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:



Compliant Reach 247:

Product Details

- Aluminum Substrate Mirrors
- Ideal for LVMR Laser Applications
- Aluminum and Gold Coating Options

Metal Substrate Mirrors are available with either a protected aluminum or gold coating and are ideal for LVMR (greater than 2000nm) laser applications. Due to the 17.5nm roughness of the diamond turned surface, these mirrors may not be suitable for UV and visible applications that require low scatter. The backs of the mirrors are machined flat and are tapped with 3 holes for easy, accurate mounting. Metal Substrate Mirrors are aluminum substrate, diamond turned metal mirrors. These mirrors are available in five diameters: 25.4, 38.1, 50.8, 76.2, and 101.6mm.

Technical Information



Compatible Mounts

