

TECHSPEC[®] 35.0mm Dia. x 70.0mm FL, NIR I, Inked, Plano-Convex Lens



Stock **#38-384-INK** 10-15 DAYS
[Other Coating Options](#)

-

1

+

A\$101.60

ADD TO CART

Qty 1-9
A\$101.60
Qty 10+
A\$91.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
35.00 ±0.025

Effective Focal Length EFL (mm):
70.00 @ 587.6nm

Back Focal Length BFL (mm): 66.04
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 6.00 ±0.10
Edge Thickness ET (mm): 1.49
Radius R₁ (mm): 36.18
Clear Aperture CA (mm): 34
f/#: 2.00
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View