

[See all 1 Products in Family](#)

Optotune 3mm Clear Aperture, VIS Coated, Electrically Focus Tunable Lens | EL-3-10-VIS-26D-FPC

See More by [Optotune](#)



Stock #37-344 **2 In Stock**

⊖ 1 ⊕ A\$280⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$280.00 each
Need More?	Request Quote

Product Downloads

General

Specialty Lens	Type:
>1,000,000,000	Lifecycles:
EL-3-10-VIS-26D-FPC	Model Number:
<5 (80% step response)	Settling Time (ms):

Physical & Mechanical Properties

3 Clear Aperture CA (mm):

10.0 Outer Diameter (mm):

4.00 Thickness (mm):

Optical Properties

Low Dispersion Polymer Substrate:

BBAR (420-900nm) Coating:

420 - 900 Wavelength Range (nm):

100 Abbe Number (v_d):

-13 to +13 diopter Focus Range (mm):
-77 to +77mm

1.300 Index of Refraction (n_d):

0.2λ @ 525nm Transmitted Wavefront Error, RMS:

3W/cm² @ 1064nm Damage Threshold, By Design:

>1 kW/cm² @ 1064nm Damage Threshold, CW:

Electrical

-120 to +120 Current (mA):

0 - 0.12 Power Consumption (W):

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Continuous Focusability
- Compact Size
- Wide Focal Adjustment Range

Optotune Focus Tunable Lenses 3mm Clear Aperture FPC Connector are easily integrated into a variety of Machine Vision applications including inspection, sorting, and bar code reading. By applying a current, the Optotune Focus Tunable Lenses 3mm Clear Aperture FPC Connector are able to quickly change shape from concave to convex, and provides an adjustment of -13 to +13 diopters (-77 to +77mm). With a small form factor of 10mm diameter x 4mm thick, low power consumption, and fast settling time, these lenses are the ideal option for OEM integration.