

3mm Dia. x 9mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-058 CLEARANCE 20+ In Stock

Other Coating Options

-

1

+

A\$32^{.80}

ADD TO CART

Volume Pricing	
Qty 1+	A\$32.80 each
Need More?	Request Quote

Product Downloads

General

	Type:
Plano-Convex Lens	

Physical & Mechanical Properties

3.00 +0.00/-0.10	Diameter (mm):
6.00	Centering (arcmin):

1.50	Center Thickness CT (mm):
------	---------------------------

1.25	Edge Thickness ET (mm):
≥2.55	Clear Aperture CA (mm):
Optical Properties	
9.00	Effective Focal Length EFL (mm):
8.01	Back Focal Length BFL (mm):
Uncoated	Coating:
N-BK7	Substrate: ☐
±1	Focal Length Tolerance (%):
4.65	Radius R ₁ (mm):
3.00	f#:
0.17	Numerical Aperture NA:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Feature Standard Designs and Specifications
- Also Available with [MgF₂ Coating](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. Commercial Grade Uncoated Plano-Convex (PCX) Lenses offer commercial quality, at an affordable price.

Technical Information

