

TECHSPEC® 3X, 65mm WD, In-Line CompactTL™ Telecentric Lens



65mm WD, 3X, In-Line Version (Left) and VIS Version (Right)

Stock **#67-314** 3-5 DAYS

- 1 + **A\$758.00**

ADD TO CART

Qty 1+

A\$758.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length excluding Threads (mm):
79.40

Horizontal Field of View, 1/2" Sensor:
2.1mm

Horizontal Field of View, 2/3" Sensor:
2.9mm

Filter Thread:
M25.5 x 0.50 (Female) with Required Adapter [#88-212](#)
Sold Separately

Maximum Diameter (mm):

18.00
Weight (g): 56
Horizontal Field of View, 1/3" Sensor: 1.6mm
Numerical Aperture NA, Object Side: 0.068
Working Distance Tolerance (mm): ±1
Number of Elements (Groups): 6 (4)
Note: CompactTL™
Typical Telecentricity @ 588nm (°): 0.091
Typical Distortion @ 588nm (%): 0.0821
Front Thread: M16 x 0.5 (Female)
Manufacturer: Edmund Optics®
Type: Telecentric Lens
Primary Magnification PMAG: 3X
Maximum Sensor Format: 2/3"
Working Distance (mm): 65
Mount: C-Mount
Style: In-Line Illumination
Aperture (f/#): f/21.9
Coating: λ/4 MgF ₂
Compatible Light Guide/Source: 1/4" (0.312") and 1/8" (0.187")
Depth of Field (mm): ±0.12mm (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 2.9 x 2.2
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View