

[See all 12 Products in Family](#)

400µm Aperture Diameter, Chrome on Glass Aperture



Stock #90-741 NEW 1 In Stock

-
1
+
A\$296^{.00}

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | A\$296.00 each |
| Need More? | Request Quote |

Product Downloads

Physical & Mechanical Properties

25.4 **Outer Diameter (mm):**

400 ± 5.0 **Fixed Aperture Diameter (µm):**

0.06 ± 0.004 **Thickness (inches):**

1.52 **Thickness (mm):**

±0.1 **Thickness Tolerance (mm):**

Optical Properties

Low Reflective Chrome

Coating:

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Chrome Coating on Glass Substrate
- Ideal for Precise Beam Control, Modulation, or Optical Alignment
- Pinhole Diameters Ranging from 10 μ m to 1,000 μ m

Chrome Coated Glass Optical Apertures are composed of soda lime float glass with low reflective chrome coating for high-contrast performance. These apertures are designed with pinhole diameters ranging from 10 μ m to 1000 μ m. The apertures have an overall diameter of 25.4mm (1") and a thickness of 1.52mm, ensuring easy integration with a wide variety of optical mounts. Chrome coating on glass provides a stable and circular aperture diameter immune to bending or creasing. Chrome Coated Glass Optical Apertures are designed to provide high-precision light control, ideal for beam shaping, spatial filtering, and alignment in advanced photonic systems.