


TECHSPEC[®] 400nm, 12.7mm Dia. x 6.35mm Thickness, Ultrafast Laser Mirror



Stock **#26-823** 14 In Stock

-

1

+

A\$168^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	A\$168.00 each
Qty 6-25	A\$149.60 each
Need More?	Request Quote

Product Downloads

General	
Laser Mirror	Type:
Physical & Mechanical Properties	
6.35 ±0.20	Thickness (mm):
12.70 +0.00/-0.10	Diameter (mm):
90	Clear Aperture (%):

Commercial Polish	Back Surface:
<3	Parallelism (arcmin):
Optical Properties	
Fused Silica (Corning 7980)	Substrate: □
10-5	Surface Quality:
45	Angle of Incidence (°):
Ultrafast (380-420nm)	Coating:
400	Design Wavelength DWL (nm):
380 - 420	Wavelength Range (nm):
λ/8	Surface Flatness (P-V):
Coating Specification: R _(avg) S & P >99.90% @ 400nm @ 45° AOI R _(avg) >99.7% @ 380 - 420nm @ 45° AOI	
Dielectric	Coating Type:
GDD Specification: ±10 fs ² @ 380 - 420nm @ 45° AOI (s-pol) ±10 fs ² @ 380 - 420nm @ 45° AOI (p-pol)	
Environmental & Durability Factors	
ML-PRF-13830B	Durability:
Regulatory Compliance	
View	Certificate of Conformance:

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- GDD as Low as ±20fs² at Design Wavelength Range
- Greater than 99.9% Reflectivity
- Ideal for Ti:sapphire and Yb:doped Ultrafast Lasers

TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors feature a multilayer dielectric coating on fused silica substrates for excellent reflectivity of greater than 99.9%, and low coefficient of thermal expansion, making them ideal for ultrafast beam transport applications. These mirrors have a group delay dispersion (GDD) of near zero at their design wavelength range, minimizing dispersion of the reflected beam. TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors are ideal for utilizing the first and second harmonic of Ti:sapphire and Yb:doped lasers for applications such as laser machining and welding.

Note: Please [contact us](#) if your application requires a TECHSPEC Low GDD Ultrafast Mirror with a custom wavelength, angle, or size.