

LightPath 357775 | 405nm Alignment, 0.60 NA Fiber Collimator w/ FC/APC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #13-550

3-5 DAYS

-

1

+

A\$432.00

ADD TO CART

Qty 1-5

A\$432.00

Qty 6+

A\$317.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):

4.00 @ 408nm

Numerical Aperture NA:

0.60

Substrate: D-Lak6
Coating: BBAR (350-500nm)
Coating Specification: R _{abs} <1.0% @ 350 - 500nm
Surface Quality: 40-20
Clear Aperture CA (mm): 4.80
f#: 0.84
Bevel: Protective bevel as needed
Connector: FC/APC
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 9.6
Lightpath Lens Code: 357775
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 350 - 500
Conjugate Distance: Infinite
Lens Included: #83-990
Alignment Wavelength (nm): 405

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant