

[See all 67 Products in Family](#)

LightPath 357775 | 405nm Alignment, 0.60 NA Fiber Collimator w/ FC/APC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#13-550** 20+ In Stock

-

1

+

A\$558⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$558.40 each
Qty 6+	A\$409.60 each
Need More?	Request Quote

Product Downloads

General	
357775	Lightpath Lens Code:
Fiber Collimator	Type:
#83-990	Lens Included:

Physical & Mechanical Properties

4.80	Clear Aperture CA (mm):
Protective as needed	Bevel:
304L Stainless Steel Housing	Construction:
11.00	Housing Diameter (mm):
9.6	Housing Length (mm):

Optical Properties

4.00 @ 408nm	Effective Focal Length EFL (mm):
0.60	Numerical Aperture NA:
D-Lak6	Substrate: □
BBAR (350-500nm)	Coating:
R _{abs} <1.0% @ 350 - 500nm	Coating Specification:
40-20	Surface Quality:
0.84	f/#:
350 - 500	Wavelength Range (nm):
Infinite	Conjugate Distance:
405	Alignment Wavelength (nm):
< 0.15	Transmitted Wavefront Error (λ, RMS):

Hardware & Interface Connectivity

FC/APC	Connector:
--------	------------

Threading & Mounting

M11 x0.5	Mount:
----------	--------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

• Easy to Integrate

• Models for FC/PC, FC/APC, and SMAConnections Available

• Four Wavelength Ranges Covering 350-1600nm

LightPath® Fiber Optic Collimators are designed to collimate light exiting a fiber to a desired beam diameter or spot size or to focus light into a fiber when used in reverse. The lenses are diffraction limited, so they can achieve spot sizes down to a few microns. Lenses also feature an antireflection coating for low back reflection. LightPath® Fiber Optic Collimators are designed so that they can be used in pairs to couple the input and output light of optical devices. Optimum performance for long-term use is ensured by the factory set and tested lens alignment. Typical applications can include use with fiber coupled lasers and pigtailed receptacles, as well as communications and data transfer.

Technical Information

