

[See all 18 Products in Family](#)

**TECHSPEC® 40mm, 60mm Radius, Metric Goniometer**



TECHSPEC® Goniometers



Stock #66-529 [CONTACT US](#)

⊖ 1 ⊕ A\$880<sup>00</sup>

ADD TO CART

Volume Pricing	
Qty 1-2	A\$880.00 each
Qty 3+	A\$768.16 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Type:  
Metric

Resolution (arcmin):  
5

**Physical & Mechanical Properties**

Type of Movement:

Goniometer	
40 x 40	<b>Stage Size (mm):</b>
±10	<b>Travel (°):</b>
Brass Stage	<b>Construction:</b>
0.5	<b>Leadscrew Pitch (mm):</b>
3	<b>Load Capacity (kg):</b>
60	<b>Radius R (mm):</b>
1.57 x 1.57	<b>Stage Size (inches):</b>
0.3	<b>Weight (kg):</b>

## Hardware & Interface Connectivity

Lead Screw	<b>Type of Drive:</b>
------------	-----------------------

## Threading & Mounting

(1) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4	<b>Mounting Threads:</b>
--	--------------------------

## Regulatory Compliance

Compliant	<b>RoHS 2015:</b>
View	<b>Certificate of Conformance:</b>
Compliant	<b>REACH 241:</b>

## Product Details


[Bottom adapter plates](#), sold separately, are required to mount 30mm and 40mm stages to standard breadboards.

- Metric and English Hole Patterns Available
- Stackable for Two-Axis Rotation
- Mechanically Compatible with our [TECHSPEC® Stages](#)

TECHSPEC® Goniometers allow for precise angular adjustment of an object about a fixed point located above the center of the mounting surface. They provide true tip and tilt adjustment of any optical component and are often used to accurately direct lasers and align mirrors in beam steering applications. These goniometers are available in with Metric and English hole patterns. TECHSPEC® Goniometers are available in different plate sizes to accommodate a host of applications. Each size is offered in several radii of movement for easily stacking into two axis configurations. To provide motion about a common point in two different axes, mount goniometer stages with smaller radii on top of those with larger radii of the same stage size.

Each goniometer stage features precision movement along a dovetail design with a vernier scale for high-resolution measurements and movement repeatability. A locking thumbscrew allows each to be held securely in place. 30mm and 40mm goniometer stages are constructed of durable black painted brass, while 70mm goniometer stages are constructed of black anodized aluminum. [Bottom adapter plates](#), sold separately, are required to mount 30mm and 40mm stages to standard breadboards; 70mm stages will mount directly.

## Technical Information



		Top Stage																					
		30mm Linear Dovelall	30mm Linear	30mm Vertical	30mm Tip/Tilt	30mm Goniometer	30mm Rotary	40mm Linear Dovelall	40mm Linear	40mm Vertical	40mm Tip/Tilt	40mm Goniometer	40mm Rotary	65mm Linear Dovelall	70mm Linear	70mm Vertical	70mm Tip/Tilt	70mm Goniometer	70mm Rotary	125mm Vertical	125mm Tip/Tilt	125mm Rotary	
Bottom Stage	30mm Linear Dovelall																						
	30mm Linear																						
	30mm Vertical																						
	30mm Tip/Tilt																						
	30mm Goniometer																						
	30mm Rotary																						
	40mm Linear Dovelall																						
	40mm Linear																						
	40mm Vertical																						
	40mm Tip/Tilt																						
	40mm Goniometer																						
	40mm Rotary																						
	65mm Linear Dovelall																						
	70mm Linear																						
70mm Vertical																							
70mm Tip/Tilt																							
70mm Goniometer																							
70mm Rotary																							
125mm Linear																							
125mm Vertical																							
125mm Tip/Tilt																							
125mm Rotary																							

