

TECHSPEC[®] 40mm Dia., 4mm Thick, NIR II Coated, $\lambda/4$ Fused Silica Window



TECHSPEC[®] $\lambda/4$ UVFused Silica Windows

Stock **#25-660** **1 In Stock**

-

1

+

A\$339²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$339.20 each
Qty 6-25	A\$268.80 each
Qty 26-49	A\$252.80 each
Need More?	Request Quote

Product Downloads

77.00

#Sorting:

General

Protective Window

Type:

Physical & Mechanical Properties

36.00

Clear Aperture CA (mm):

40.00 +0.00/-0.10	Diameter (mm):
4.00 ±0.10	Thickness (mm):
<1	Parallelism (arcmin):
Protective as needed	Bevel:
90	Clear Aperture (%):
Fine Ground	Edges:
0.16	Poisson's Ratio:
73	Young's Modulus (GPa):
522.00	Knoop Hardness (kg/mm²):

Optical Properties	
NIR II (750-1550nm)	Coating:
Fused Silica (Corning 7980)	Substrate: ☐
1.458	Index of Refraction (n _d):
40-20	Surface Quality:
λ/4	Transmitted Wavefront, P-V:
67.8	Abbe Number (v _d):
R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm	Coating Specification:
750 - 1550	Wavelength Range (nm):

8 J/cm² @ 1064nm, 10ns	Damage Threshold, Reference:
------------------------	------------------------------



Material Properties	
2.20	Density (g/cm³):
0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Available Uncoated or BBAR Coated for UV, Visible, and NIR
 - Ideal for Imaging Applications
 - Circular and Rectangular Sizes from 5 to 200mm
 - [1λ](#) or [λ/10](#) UV Fused Silica Windows Also Available
- TECHSPEC® λ/4 UV Fused Silica Windows are manufactured with 40-20 surface quality and λ/4 transmitted wavefront error specifications, making them ideal for imaging applications. Featuring UV fused silica substrates, these windows provide high transmission from the ultraviolet (UV) through the visible and near-infrared (NIR). Broadband anti-reflection (BBAR) coating options are available to minimize reflection losses and increase transmission. TECHSPEC λ/4 UV Fused Silica Windows are used in optical imaging applications, in low to medium powered laser applications, and as protective windows, especially in applications requiring transmission of UV light.

Technical Information



FUSED SILICA																																			
Uncoated Fused Silica Typical Transmission <table border="1"><caption>Approximate data for Uncoated Fused Silica Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>92</td></tr><tr><td>400</td><td>94</td></tr><tr><td>600</td><td>94</td></tr><tr><td>800</td><td>94</td></tr><tr><td>1000</td><td>94</td></tr><tr><td>1200</td><td>94</td></tr><tr><td>1400</td><td>92</td></tr><tr><td>1600</td><td>94</td></tr><tr><td>1800</td><td>94</td></tr><tr><td>2000</td><td>94</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	92	400	94	600	94	800	94	1000	94	1200	94	1400	92	1600	94	1800	94	2000	94	2200	90	Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra. Click Here to Download Data										
Wavelength (nm)	Transmission T (%)																																		
200	92																																		
400	94																																		
600	94																																		
800	94																																		
1000	94																																		
1200	94																																		
1400	92																																		
1600	94																																		
1800	94																																		
2000	94																																		
2200	90																																		
Fused Silica with MgF₂ Coating Typical Transmission <table border="1"><caption>Approximate data for MgF2 Coated Fused Silica Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>94</td></tr><tr><td>400</td><td>96</td></tr><tr><td>600</td><td>96</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>95</td></tr><tr><td>1200</td><td>95</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>95</td></tr><tr><td>1800</td><td>95</td></tr><tr><td>2000</td><td>95</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	94	400	96	600	96	800	95	1000	95	1200	95	1400	93	1600	95	1800	95	2000	95	2200	90	Typical transmission of a 3mm thick fused silica window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm (N-BK7)}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data										
Wavelength (nm)	Transmission T (%)																																		
200	94																																		
400	96																																		
600	96																																		
800	95																																		
1000	95																																		
1200	95																																		
1400	93																																		
1600	95																																		
1800	95																																		
2000	95																																		
2200	90																																		
Fused Silica with UV-AR Coating Typical Transmission <table border="1"><caption>Approximate data for UV-AR Coated Fused Silica Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>75</td></tr><tr><td>250</td><td>98</td></tr><tr><td>300</td><td>99</td></tr><tr><td>350</td><td>99</td></tr><tr><td>400</td><td>99</td></tr><tr><td>425</td><td>100</td></tr><tr><td>500</td><td>99</td></tr><tr><td>600</td><td>98</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>85</td></tr><tr><td>1200</td><td>80</td></tr><tr><td>1400</td><td>78</td></tr><tr><td>1600</td><td>76</td></tr><tr><td>1800</td><td>75</td></tr><tr><td>2000</td><td>75</td></tr><tr><td>2200</td><td>76</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	75	250	98	300	99	350	99	400	99	425	100	500	99	600	98	800	95	1000	85	1200	80	1400	78	1600	76	1800	75	2000	75	2200	76	Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.75\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.5\% @ 370 - 420\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																																		
200	75																																		
250	98																																		
300	99																																		
350	99																																		
400	99																																		
425	100																																		
500	99																																		
600	98																																		
800	95																																		
1000	85																																		
1200	80																																		
1400	78																																		
1600	76																																		
1800	75																																		
2000	75																																		
2200	76																																		

	
Fused Silica with UV-VIS Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}$$R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-EXT Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-NIR Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}$$R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}$$R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% \text{ @ } 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

