

TECHSPEC[®] 40mm Dia. x 120mm FL, YAG-BBAR Coated, Achromatic Lens



YAG-BBAR Coated Achromatic Lenses



Stock #19-419 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$265.60

ADD TO CART

Qty 1-5

A\$265.60

Qty 6+

A\$212.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Effective Focal Length EFL (mm):

120.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 111.00
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 39.00
Centering (arcmin): <1
Center Thickness CT (mm): 13.80 ±0.20
Center Thickness CT 1 (mm): 9.6 ±0.10
Center Thickness CT 2 (mm): 4.2 ±0.10
Radius R ₁ (mm): 65.22
Radius R ₂ (mm): -62.03
Radius R ₃ (mm): -1240.67
Edge Thickness ET (mm): 10.51
Substrate:  N-SSK8 / N-SF10
Surface Quality: 40-20
f/#: 3.00
Numerical Aperture NA: 0.17
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 500 - 1100

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View