

TECHSPEC® 40mm Dia. x 400mm FL, NIR II Coated, Double-Convex Lens



Stock **#67-672** CLEARANCE 3-5 DAYS
[Other Coating Options](#)

- 1 +

A\$31.92

ADD TO CART

Qty 1+
A\$31.92
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Back Focal Length BFL (mm):
397.35

Effective Focal Length EFL (mm):
400.00

Coating: NIR II (750-1550nm)
Coating Specification: R_{abs} ≤1.5% @ 750 - 800nm R_{abs} ≤1.0% @ 800 - 1550nm R_{avg} ≤0.7% @ 750 - 1550nm
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Center Thickness CT (mm): 8.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 7.03
Radius R₁=R₂ (mm): 412.09
Clear Aperture CA (mm): 39.00
f#: 10.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Numerical Aperture NA: 0.05
Type: Double-Convex Lens
Wavelength Range (nm): 750 - 1550
Damage Threshold, Reference:  8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Reach 224: Compliant
Certificate of Conformance: View