

TECHSPEC® 40mm Dia. x 60mm FL YAG-BBAR Coated, Inked, Double-Convex Lens



YAG-BBAR Coated Double-Convex (DCX) Lenses



Stock **#89-283-INK** [CONTACT US](#)

- 1 +

A\$128.00

ADD TO CART

Qty 1-9
A\$128.00
Qty 10+
A\$115.20
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
40.00 ±0.025

Back Focal Length BFL (mm):
57.1

Effective Focal Length EFL (mm): 60.00
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Substrate:  N-BK7
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 8.80
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.00
Radius R₁=R₂ (mm): 60.56
Clear Aperture CA (mm): 39.00
f/#: 1.5
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.33
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View