

TECHSPEC<sup>®</sup> 40mm Dia. x 750mm FL, VIS 0° Coated, Achromatic Lens



Stock **#67-333** 20+ In Stock

☐ Other Coating Options

-

1

+

A\$310<sup>.40</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | A\$310.40 each                |
| Qty 6-25       | A\$248.00 each                |
| Qty 26-49      | A\$233.60 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

SPECIFICATIONS

General

Type:

|                                  |                             |
|----------------------------------|-----------------------------|
| Achromatic Lens                  |                             |
| Physical & Mechanical Properties |                             |
| 40.00 +0.0/-0.025                | Diameter (mm):              |
| 39.00                            | Clear Aperture CA (mm):     |
| <1                               | Centering (arcmin):         |
| 8.00 ±0.20                       | Center Thickness CT (mm):   |
| 4.00 ±0.10                       | Center Thickness CT 1 (mm): |
| 4.00 ±0.10                       | Center Thickness CT 2 (mm): |
| 7.36                             | Edge Thickness ET (mm):     |
| Protective as needed             | Bevel:                      |

|                                      |                                             |
|--------------------------------------|---------------------------------------------|
| Optical Properties                   |                                             |
| 750.00                               | Effective Focal Length EFL (mm):            |
| ±0.2                                 | Focal Length Tolerance (%):                 |
| 744.37                               | Back Focal Length BFL (mm):                 |
| 587.6                                | Focal Length Specification Wavelength (nm): |
| 315.18                               | Radius R <sub>1</sub> (mm):                 |
| -506.69                              | Radius R <sub>2</sub> (mm):                 |
| -∞                                   | Radius R <sub>3</sub> (mm):                 |
| N-BK7 / N-SF5                        | Substrate: <input type="checkbox"/>         |
| 40-20                                | Surface Quality:                            |
| 18.75                                | f/#:                                        |
| 0.03                                 | Numerical Aperture NA:                      |
| VIS 0° (425-675nm)                   | Coating:                                    |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm | Coating Specification:                      |
| 1.5λ                                 | Power (P-V) @ 632.8nm:                      |
| λ/4                                  | Irregularity (P-V) @ 632.8nm:               |
| 425 - 675                            | Wavelength Range (nm):                      |


|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| Compliant             | Reach 219:                  |
| View                  | Certificate of Conformance: |

## PRODUCT DETAILS

- Designed for 0° Angle of Incidence
- Less Than 0.4% Reflectance Per Surface from 425 - 675nm
- MgF<sub>2</sub> and VIS-NIR Coated Achromats Also Available

TECHSPEC® VIS 0° Coated Achromatic Lenses consist of two optical components cemented together to form an achromatic doublet. The doublet is computer optimized to correct for on-axis spherical and chromatic aberrations. Achromatic lenses are best for applications involving multi-color (white light) imaging due to their specific doublet lens pairing that enables them to correct the color separation inherent in glass. TECHSPEC® VIS 0° Coated Achromatic Lenses provide optimized transmission for 425 – 675nm, reducing average reflection to 0.4%. MgF<sub>2</sub> and VIS-NIR Coated Achromats are also available on our website.

## TECHNICAL INFORMATION



## COATING CURVES

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## COMPATIBLE MOUNTS