

[See all 40 Products in Family](#)

TECHSPEC® 40mm, Protected Gold, N-BK7 Right Angle Prism Mirror (Leg Coated)



Stock #25-697 **2 In Stock**

A\$572.⁸⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | A\$572.80 each |
| Qty 6-25 | A\$457.60 each |
| Qty 26-49 | A\$430.40 each |
| Need More? | Request Quote |

Product Downloads

General

Right Angle Mirror Type:

Physical & Mechanical Properties

36.0 Clear Aperture CA (mm):

±0.1 Dimensional Tolerance (mm):

Protective as needed **Bevel:**

90.00 **Clear Aperture (%):**

56.60 **Length of Hypotenuse (mm):**

40.00 **Length of Legs (mm):**

Optical Properties

Protected Gold (700-10000nm) **Coating:**

N-BK7 **Substrate:**

40-20 **Surface Quality:**

±2 **Angle Tolerance (arcmin):**

Coating Specification:
R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm

700 - 10000 **Wavelength Range (nm):**

Metal **Coating Type:**

0.8 J/cm² @ 1064nm, 10ns **Damage Threshold, Reference:**

1.25 **Power (fringes) @ 632.8nm:**

0.50 **Irregularity (fringes) @ 632.8nm:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Splits Input Image Into Two Paths Separated by 180°
- Variety of Sizes and Broadband Coatings Available
- Additional [Right Angle Prism](#) Options Available

TECHSPEC® Right Angle Prism Mirrors (Leg Coated) are constructed from right angle prisms with a mirror coating on the two legs and an uncoated hypotenuse. The mirrored surfaces form a precise 90° angle, ideal for splitting an image from a single imaging lens onto two different cameras, or for combining two images onto a single camera.

Technical Information



| Stock No. | Coating | A | B | C |
|-----------|--------------------------------|------|---------|------|
| #49-412 | Enhanced Aluminum (450-650nm) | 5mm | 7.1mm | 5mm |
| #65-847 | Protected Gold (700-10000nm) | | | |
| #21-185 | Protected Silver (450-10000nm) | | | |
| #47-004 | Enhanced Aluminum (450-650nm) | 10mm | 14.1mm | 10mm |
| #47-237 | Protected Gold (700-10000nm) | | | |
| #21-186 | Protected Silver (450-10000nm) | | | |
| #49-413 | Enhanced Aluminum (450-650nm) | 15mm | 21.2mm | 15mm |
| #65-848 | Protected Gold (700-10000nm) | | | |
| #21-187 | Protected Silver (450-10000nm) | | | |
| #49-414 | Enhanced Aluminum (450-650nm) | 20mm | 28.3mm | 20mm |
| #65-849 | Protected Gold (700-10000nm) | | | |
| #21-188 | Protected Silver (450-10000nm) | | | |
| #47-005 | Enhanced Aluminum (450-650nm) | 25mm | 35.4mm | 25mm |
| #47-238 | Protected Gold (700-10000nm) | | | |
| #21-189 | Protected Silver (450-10000nm) | | | |
| #47-006 | Enhanced Aluminum (450-650nm) | 50mm | 70.7mm | 50mm |
| #47-239 | Protected Gold (700-10000nm) | | | |
| #21-190 | Protected Silver (450-10000nm) | | | |
| #47-309 | Enhanced Aluminum (450-650nm) | 75mm | 106.1mm | 75mm |
| #47-310 | Protected Gold (700-10000nm) | | | |
| #21-191 | Protected Silver (450-10000nm) | | | |

