

TECHSPEC[®] 40mm Dia. x 750mm FL, VIS-NIR Coated, Achromatic Lens



Stock #67-336 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$288.00

ADD TO CART

Qty 1-5

A\$288.00

Qty 6+

A\$230.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Effective Focal Length EFL (mm):
750.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 744.37
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 39.00
Centering (arcmin): <1
Center Thickness CT (mm): 8.00 ±0.20
Center Thickness CT 1 (mm): 4.00 ±0.10
Center Thickness CT 2 (mm): 4.00 ±0.10
Radius R₁ (mm): 315.18
Radius R₂ (mm): -506.69
Radius R₃ (mm): ∞
Edge Thickness ET (mm): 7.36
Substrate: ☐ N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 18.75
Numerical Aperture NA: 0.03
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View