


457nm 70 x 375mm META[®] holoOPTIX[®] FLEX Notch Filter



70 x 375mm META[®] holoOPTIX[®] FLEX Notch Filter

Stock **#23-030** CLEARANCE **3 In Stock**

-

1

+

A\$400⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$400.00 each
Need More?	Request Quote

Product Downloads

General	
Notch Filter	Type:
Physical & Mechanical Properties	
70 x 375	Dimensions (mm):
0.31	Thickness (mm):
Optical Properties	

>4.0	Optical Density OD (Average):
457.00	Center Wavelength CWL (nm):
77% (400-435nm) 87% (500-1500nm)	Transmission (%):
8 (Typical)	Spectral Bandwidth @ OD1:

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- >OD 4.0 (Typical)
 - Broad Transmission Range
 - Unique Large Flexible Design
 - META® refers to the registered trademark of Meta Materials Inc.
- META® holoOPTIX® Notch Filters are ideal for laser analysis applications requiring specific wavelength rejection and high transmission of all other wavelengths. Available in either a standard 25.4mm rigid mounted configuration (STRATA) or in a unique 375mm x 70mm flexible configuration (FLEX), these filters can be used in fluorescence or Raman spectrometers to eliminate unwanted noise from the pump laser source to obtain the optimum signal-to-noise ratio. The flexible design can be easily be cut for system prototyping and integration. META® holoOPTIX® Notch Filters center wavelengths can be tuned by adjusting the angle of incidence while maintaining consistent notch center wavelengths for both p- and s- polarizations, even at high angles of incidence.

Technical Information

