


TECHSPEC® 4.0X SilverTL™ Telecentric Lens



4.0X Magnification



Stock **#58-432** 3-5 DAYS

1

A\$1,112.00

ADD TO CART

Qty 1+

A\$1,112.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length excluding Threads (mm):
249.00

Horizontal Field of View, 1/2" Sensor:
1.6mm

Horizontal Field of View, 2/3" Sensor:
2.2mm

Filter Thread:
M58 x0.75 (Female)

Maximum Diameter (mm): 61.00
Weight (g): 733
Horizontal Field of View, 1/3" Sensor: 1.2mm
Numerical Aperture NA, Object Side: 0.32
Working Distance Tolerance (mm): ±3
Stock No. of Mounting Clamp: #56-870 Sold Separately
Resolution, Image Space MTF @ f/10: >40% @ 40 lp/mm
Number of Elements (Groups): 10 (9)
Note: SilverTL™
Typical Telecentricity @ 588nm (°): <0.050
Typical Distortion @ 588nm (%): <0.060
Type: Telecentric Lens
Primary Magnification PMAG: 4X
Maximum Sensor Format: 2/3"
Working Distance (mm): 44.00
Mount: C-Mount
Aperture (f/#): f/6 - f/22
Coating: 425 - 675nm BBAR
Construction: Anodized Aluminum
Depth of Field (mm): ±0.03 at f/10 (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 2.2 x 1.6
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View