

TECHSPEC®

4.25" Diameter x 34" FL Protected Aluminum, Parabolic Mirror



Stock #32-067-522

CONTACT US

-

1

+

A\$697.60

ADD TO CART

Qty 1-9

A\$697.60

Qty 10+

A\$593.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Substrate:

BOROFLAT®

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 4.25 +0.06/-0
Diameter (mm): 108.00 +1.5/-0
Effective Focal Length EFL (inches): 34.0
Effective Focal Length EFL (mm): 863.60
Radius of Curvature (mm): 1,727.20
Aperture (f/#): f/8
Coating: Protected Aluminum (400-2000nm)
Coating Specification: Ravg >85% @ 400 - 700nm Ravg >90% @ 400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 98
Edge Thickness ET (inches): 0.75
Edge Thickness ET (mm): 19.10
Type: Parabolic Mirror
Wavelength Range (µm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: 0.3 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant