


# 450nm, 12.5mm Dia., OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock #15-211 3-5 DAYS

- 1 + **A\$131.20**

ADD TO CART

Qty 1-9

A\$131.20

Qty 10+

A\$118.08

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):  
12.50 +0.00/-0.20

Angle of Incidence (°):  
0

Optical Density OD (Average):  
≥2.0

|                                                                                                                                |
|--------------------------------------------------------------------------------------------------------------------------------|
| <b>Cut-On Wavelength (nm):</b><br>450.00 ±9                                                                                    |
| <b>Substrate:</b>  <a href="#">BOROFLOAT®</a> |
| <b>Coating:</b><br>Hard Coated                                                                                                 |
| <b>Rejection Wavelength (nm):</b><br>200 - 425                                                                                 |
| <b>Surface Quality:</b><br>60-40                                                                                               |
| <b>Thickness (mm):</b><br>2.00 ±0.10                                                                                           |
| <b>Transmission (%):</b><br>≥85                                                                                                |
| <b>Transmission Wavelength (nm):</b><br>475 - 1600                                                                             |
| <b>Type:</b><br>Longpass Filter                                                                                                |
| <b>Clear Aperture (%):</b><br>90                                                                                               |
| <b>Environmental Durability:</b><br>ML-STD-810F, Section 507.4                                                                 |
| <b>Physical Durability:</b><br>ML-C-48497A Section 3.4.1                                                                       |
| <b>Wavelength Range (nm):</b><br>200 - 1600                                                                                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |