

TECHSPEC[®] 45° AOI, 25.0mm Square, Cold Mirror



TECHSPEC High Performance Cold Mirrors

Stock **#64-448** 20+ In Stock

-

1

+

A\$96⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	A\$96.00 each
Qty 10-25	A\$86.40 each
Qty 26-49	A\$82.40 each
Need More?	Request Quote

Product Downloads

General	
Cold Mirror	Type:
Physical & Mechanical Properties	
3.30 ±0.2	Thickness (mm):
25.0 x 25.0	Dimensions (mm):



+0.0/-0.2	Dimensional Tolerance (mm):
25.00	Length (mm):
25.00	Width (mm):
Optical Properties	
Dichroic Filter	Transmission (%):
Dielectric	Coating Type:
Cold Mirror, 45°	Coating:
4 - 6λ	Surface Flatness (P-V):
425 - 1150	Wavelength Range (nm):
 BOROFLOAT®	Substrate: 
45	Angle of Incidence (°):
Coating Specification: R _{avg} ≥95% @400 - 690nm and T _{avg} ≥90% @ 750 - 1200nm AR Coating: R _{avg} <1% @ 700 - 1150nm	
80-50	Surface Quality:
Regulatory Compliance	
 Compliant	RoHS 2015:
 View	Certificate of Conformance:
 Compliant	Reach 247:

Product Details

- >95% Reflection from 400 - 690nm
- >90% Transmission from 750 - 1200nm
- Optimized for 0° or 45° Angle of Incidence

TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

Technical Information



Quote Your Size

Compatible Mounts

