

TECHSPEC[®] 4.5mm Dia. x 4.5mm FL VIS-EXT Coated, Double-Convex Lens



Stock **#89-122** 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$104.00

ADD TO CART

Qty 1-9
A\$104.00
Qty 10+
A\$93.60
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
4.50 +0.000/-0.025

Back Focal Length BFL (mm):
3.7

Effective Focal Length EFL (mm):

4.50
Coating: VS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: 
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): 30-45, typical
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.60
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.8
Radius R₁=R₂ (mm): 6.58
Clear Aperture CA (mm): 4.05
f/#: 1
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant