

TECHSPEC®

4.5mm, f/11 Ci Series Fixed Focal Length Lens



4.5mm Focal Length

Stock **#87-556** 3-5 DAYS



1



A\$366.00

ADD TO CART

Qty 1+

A\$366.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Iris Option:
Fixed

Length (mm):
32.14

Horizontal Field of View, 1/2" Sensor:
53.9mm - 69.4°

Filter Thread:
M58 x0.75 with required adapter [#87-425](#)

Maximum Diameter (mm):
40

Weight (g): 66
Horizontal Field of View, 1/3" Sensor: 44.0mm - 59.2°
Maximum Rear Protrusion (mm): 3.4
Maximum Image Circle (mm): 9.00
Numerical Aperture NA, Object Side: 0.0052
Horizontal Field of View @ Max Sensor Format: 72.0mm - 84.7°
Number of Elements (Groups): 7 (6)
Horizontal Field of View, 1/1.8" Sensor: 72.0mm - 84.7°
Front Thread: M40.0 x0.5 (Male)
Type: Fixed Focal Length Lens
Diameter (mm): 26.50
Focal Length FL (mm): 4.50
Primary Magnification PMAG: 0.117
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 25 - ∞
Mount: C-Mount
Aperture (f/#): f/11
Coating: 425 - 675nm BBAR
Coating Specification: 425 - 675nm BBAR
Entrance Pupil Position (mm): 14.4
Horizontal Field of View, 1/4" Sensor: 32.0mm - 45.2°
Object Space Principal Plane (mm): 17.89
Image Space Principal Plane (mm): 6.51
Field of View at Max Sensor Format: Horizontal: 72mm - 84.7° Vertical: 50.5mm - 66.1° Diagonal: 98.3mm - 100°
Maximum Distortion (%): -15.83
Exit Pupil Position (mm): -9
Lens Wavelength Range: VIS
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View