

TECHSPEC® 4X, VIS-NIR Vega® Broadband Beam Expander



TECHSPEC® Vega™ Broadband Beam Expanders

Stock **#19-406** 3-5 DAYS

⊖ 1 ⊕ **A\$678.40**

ADD TO CART

Qty 1+

A\$678.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Laser VIS-NIR (500-1090nm)

Design Wavelength DWL (nm):
Broadband

Entrance Aperture (mm):
7.5

Exit Aperture (mm):

26
Expansion Power: 4X
Substrate: ☐ Fused Silica
Length (mm): 91.90
Mounting Threads: Input: Male M30 x 1 Output: Female M34 x 0.5
Transmission (%): >95.0 (nominal)
Type: Beam Expander
Weight (g): 160
Housing Diameter (mm): 39.95
Transmitted Wavefront, P-V: <i>λ</i> /10 for 4.0mm input beam (nominal, <i>λ</i> = DWL)
Coating Specification: Ravg ≤1.5% @ 500 - 1090nm @ 0° AOI
Wavelength Range (nm): 500 - 1090
Style: Fixed Magnification
Damage Threshold, By Design: ☐ 2 J/cm ² @ 1064nm, 20ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View