

TECHSPEC[®] 45mm, VIS 0° Coated, Penta Prism



Stock #48-603 CLEARANCE 5 In Stock

-

1

+

A\$152^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$152.00 each
Need More?	Request Quote

Product Downloads

General

Type:

Penta Prism

Physical & Mechanical Properties

Length (mm):

45.00

Dimensional Tolerance (mm):

±0.10

Bevel:

Protective as needed

Length of Legs (mm):


45.00	
Optical Properties	
Coating:	VS 0° & Aluminized
Substrate:	N-BK7
Surface Quality:	60-40
Image Orientation:	Right-Handed
Coating Specification:	Entrance/Exit Faces: R _{avg} ≤0.4% @ 425 - 675nm Reflecting Surfaces: R _{avg} >85% @ 400 - 700nm w/Black Overpaint
Ray Deviation (°):	90
Wavelength Range (nm):	425 - 675
Damage Threshold, By Design:	Entrance & Exit Faces: 5 J/cm2 @ 532nm, 10ns Reflecting Surfaces: 0.3 J/cm2 @ 532 & 1064nm, 10ns
Beam Deviation Tolerance (arcmin):	±5
Power (fringes) @ 632.8nm:	1.00
Irregularity (fringes) @ 632.8nm:	0.25
Regulatory Compliance	
RoHS 2015:	Compliant
Reach 223:	Compliant
Certificate of Conformance:	View

Product Details


- Ray Deviation of 90°
- Right Handed Image
- Optical Tool for Defining a Right Angle
- Additional [Penta Prism](#) Options Available

TECHSPEC® N-BK7 Penta Prisms are five-sided prisms featuring a ray deviation of 90° and a right-handed image. The reflecting surfaces are aluminized. Slight movement of the prism does not affect the true right angle at which light rays are reflected, making a penta prism the ideal optical tool for defining a right angle in an optical system. TECHSPEC® N-BK7 Penta Prisms are made from precision N-BK7 for use in a variety of visible light applications. These prisms are offered with a VS 0° or MgF2 coating, in a variety of sizes.

Technical Information




Penta Prism Ray Path



Penta Prism Tunnel Diagram

Stock No.	Coating	Dimensions	
		A	B
#85-159	MS 0°	0.50	0.60
#85-160	MS 0°	1.00	1.20
#45-112	MgF ₂	5.00	6.10
#48-595	MS 0°		
#32-030	MgF ₂	10.00	11.95
#48-596	MS 0°		
#43-502	MgF ₂	15.00	15.96
#48-597	MS 0°		
#31-051	MgF ₂	20.00	21.65
#48-598	MS 0°		
#42-779	MgF ₂	25.00	27.90
#47-458	MgF ₂		
#48-599	MS 0°		
#45-073	MgF ₂	30.00	32.47
#48-600	MS 0°		
#45-402	MgF ₂	35.00	37.88
#48-601	MS 0°		
#45-674	MgF ₂	40.00	43.30
#48-602	MS 0°		
#45-675	MgF ₂	45.00	48.71
#48-603	MS 0°		
#45-676	MgF ₂	50.00	54.12
#47-459	MgF ₂		
#48-604	MS 0°		



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
-