

TECHSPEC® 464, 542 & 639nm, 12.5mm Dia., Tri-Band Filter



Multi-Band Fluorescence Bandpass Filters

Stock **#87-238** 3-5 DAYS



1



A\$544.00

ADD TO CART

Qty 1-9

A\$544.00

Qty 10+

A\$452.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.1

Angle of Incidence (°):
0

Bandwidth (nm):
23 @464nm
27 @542nm

42 @ 639nm
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 8.81
Substrate:  Fused Silica (Corning 7980)
Coating: Hard Coated
Surface Quality: 60-40
Transmission (%): >90
Type: Bandpass Filter
Blocking Wavelength Range (nm): 250 - 1100
Construction: Mounted in Black Anodized Ring
Compatible Fluorophore: CFP/YFP/Texas Red Emission
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2
Mount Thickness (mm): 3.5 ±0.1
Substrate Thickness (mm): 2.00 ±0.25
Multi-Band Center Wavelengths (nm): 464, 542, 639

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant