

4X to 20X Multi-Function Target



Stock **#56-076** **4 In Stock**

-

1

+

A\$2,688^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	A\$2,688.00 each
Qty 5+	A\$2,554.88 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
1 x3	Dimensions (inches):
6.35	Thickness (mm):
±1.0	Overall Accuracy (µm):
1.00	Parallelism (arcmin):
Optical Properties	

Coating:	
Evaporated Chrome Pattern	
Substrate:	
Fused Silica (Corning 7980)	
Surface Quality:	
20-10	
Surface Flatness (P-V):	
3 - 4λ	

Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 240:	
Compliant	

Product Details


- Designed for Measurement Calibration; Ideal for Microscopes and Machine Vision Systems
- Includes Ronchi Rulings, Concentric Circles, Square Grids , and a Linear Microscale
- Two Targets Available for Different Magnifications
- NIST Certificate of Accuracy Included

Use these "all-in-one" targets to measure microscope and vision system parameters, without separate calibration targets. Targets will test and calibrate our Mtutoyo objectives, Zeiss microscopes, and high magnification video lenses for resolution, distortion, and depth of field (DOF). Targets include variable frequency Ronchi rulings, sets of grids and concentric circles with varying line spacings and widths, a microscale, and edge blocks to prop up target for DOF measurements. A user information card, complete manual on CD, and NIST certificate are provided.


Use Low Frequency Target for optical systems with 4X to 20X objectives. Target is useful for machine vision systems with low magnifications and long focal distances.

Use High Frequency Target for optical systems with 20X to 100X objectives. Target is useful for microscopes and other systems with high magnifications and short focal distances.

Technical Information

Outer Diameter (mm)	Line Spacing (mm)	Line Width (μm)
5.0	0.25	20
4.0	0.25	15
3.0	0.25	10
2.0	0.10	7.5
1.0	0.10	5
		


Width (mm)	Line Spacing (mm)	Line Width (μm)
4.5	0.25	20
4.5	0.25	15
4.5	0.25	10
4.5	0.10	15
4.5	0.10	10
4.5	0.10	5
2.55	0.075	10
2.55	0.075	5
2.55	0.050	5
2.55	0.050	2.5




Range (lp/mm)	Frequency Change (lp/mm)
60 - 380	20

Length (mm)	Divisions/mm	Microns/divisions
0 - 68.2	20	50

Outer Diameter (mm)	Line Spacing (mm)	Line Width (μm)
3.0	0.25	10
2.0	0.10	7.5
1.5	0.10	5
1.0	0.05	5
1.0	0.05	2.5



Width (mm)	Line Spacing (mm)	Line Width (μm)
3.0	0.25	10
3.0	0.25	7.5
3.0	0.25	5
3.0	0.10	10
3.0	0.10	7.5
3.0	0.10	5
2.55	0.075	10
2.55	0.075	5
2.55	0.050	5
2.55	0.050	2.5



Range (lp/mm)	Frequency Change (lp/mm)
240 - 600	10

Length (mm)	Divisions/mm	Microns/divisions
0 - 68.2	20	50