

[See all 102 Products in Family](#)

**TECHSPEC® 5.0mm Diameter x 10.0mm FL, 405nm V-Coat, PCX Lens**



633nm Laser Line Coated Plano-Convex(PCX) Lenses



Stock #88-964 **14 In Stock**

[Other Coating Options](#)

1 **A\$95<sup>20</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-9	<b>A\$95.20</b> each
Qty 10-25	<b>A\$86.40</b> each
Qty 26-49	<b>A\$76.00</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Plano-Convex Lens **Type:**

**Physical & Mechanical Properties**

**Diameter (mm):**

5.00 +0.0/-0.025

<3  
Centering (arcmin):

1.64 ±0.05  
Center Thickness CT (mm):

1.00  
Edge Thickness ET (mm):

4.5  
Clear Aperture CA (mm):

Protective as needed  
Bevel:

## Optical Properties

10.00 @ 587.6nm  
Effective Focal Length EFL (mm):

8.92  
Back Focal Length BFL (mm):

Laser V-Coat (405nm)  
Coating:

$R_{\text{abs}} < 0.25\%$  @ 405nm  
Coating Specification:

N-BK7  
Substrate:

40-20  
Surface Quality:

1.5λ  
Power (P-V) @ 632.8nm:

λ/4  
Irregularity (P-V) @ 632.8nm:

±1  
Focal Length Tolerance (%):

5.17  
Radius  $R_1$  (mm):

2.00  
f##:

0.25  
Numerical Aperture NA:

405  
Design Wavelength DWL (nm):

3 J/cm<sup>2</sup> @ 405nm, 10ns  
Damage Threshold, By Design:

## Regulatory Compliance

Compliant  
RoHS 2015:

View  
Certificate of Conformance:

Compliant  
Reach 235:

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- <0.25% Reflection at 405nm for Diode Applications
- BBAR Coating Options Also Available: [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
- 405nm, [532nm](#), [633nm](#), [785nm](#), [980nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

TECHSPEC® 405nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC® 405nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: [532nm](#), [633nm](#), [785nm](#), [980nm](#), [1064nm](#), and [1550nm](#). Other coating options are available, including [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#).

**LASER OPTICS** MADE BY EDMUND OPTICS®

LEARN MORE

## Technical Information



## Compatible Mounts

---