

TECHSPEC® 50 x 50mm Protected Gold Coated, λ /10 ZERODUR® Mirror



Stock **#39-870** 3-5 DAYS

- 1 + **A\$384.00**

ADD TO CART

Qty 1-5
A\$384.00
Qty 6+
A\$307.20
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
 λ /10 (measured before coating)

Substrate: 

Back Surface:
Commercial Polish

Surface Quality:

20-10
Dimensions (mm): 50.0 x 50.0 +0.00/-0.20
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 5.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 700 - 10000
Length (mm): 50.00
Width (mm): 50.00
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.1
Damage Threshold, Reference: ☐ 0.8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant