

50.8mm Dia. 1064nm $\lambda/4$ Quartz Waveplate Zero Order



Stock #26-738 NEW 3-5 DAYS

- 1 + **A\$2,672.00**

ADD TO CART

Qty 1+
A\$2,672.00

Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
35.00

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm):
1064

Diameter (mm):
50.80 +0.00/-0.25

Substrate: ☐
Crystal Quartz

Retardance: λ/4
Surface Quality: 20-10
Thickness (mm): 6.00 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/8 @ 632.8nm
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/300
Temperature Coefficient (λ/°C): 0.0001
Coating Specification: R _{abs} <0.2% @ on each surface
Damage Threshold, By Design: ☐ >10 J/cm² @ 1064 nm, 10ns
Retardance Order: 0
Configuration: Air spaced

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant