

TECHSPEC® 50.8mm Dia. x 6.35mm 532nm/1064nm, Dual Band Laser Mirror



Stock **#20-612** 3-5 DAYS

- 1 + **A\$438.40**

ADD TO CART

Qty 1-5
A\$438.40
Qty 6+
A\$388.80
Volume Pricing
Request Quote

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):
>90

Back Surface: Commercial Polished
Reflection at DWL (%): 99.5
Coating Specification: R_{abs} >99.5% @ 532 & 1064nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (532, 1064nm)
Design Wavelength DWL (nm): 532, 1064
Diameter (mm): 50.80 +0.0/-0.2
Thickness (mm): 6.35 ±0.2
Angle of Incidence (°): 45
Substrate: Fused Silica (Corning 7980)
Damage Threshold, Reference: 15 J/cm² @20ns @ 532nm 20 J/cm² @20ns @ 1064nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View