

50.8mm Dia. x 76.2mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF₂) DCX Lens
| CF-BX-50-76

See More by [ISP Optics](#)



Calcium Fluoride Double-Convex (DCX) Lenses

Stock #24-771

CONTACT US

-

1

+

A\$952.00

ADD TO CART

Qty 1-9
A\$952.00
Qty 10+
A\$856.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.80 +0.00/-0.13

Effective Focal Length EFL (mm):
76.20 @ 5µm

Coating: Uncoated
Substrate: Calcium Fluoride (CaF₂)
Surface Quality: 60-40
Irregularity (P-V) @ 632.8nm: λ
Centering (arcmin): <3
Bevel: Protective bevel as needed
Center Thickness CT (mm): 14.60 ±0.20
Edge Thickness ET (mm): 3.00
Radius R₁ (mm): 58.73
Radius R₂ (mm): 58.73
Clear Aperture CA (mm): 45.72
f/#: 1.50
Focal Length Tolerance (%): ±2
Numerical Aperture NA: 0.33
Type: Double-Convex Lens
Wavelength Range (nm): 300 - 8000
Model Number: CF-BX-50-76

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View